

**CP sealing ring, DI25, Clamping Ø (1 mm increments): 16 mm****Order data**

Order number	309667 16
GTIN	2050001705181
Item class	34F

Description**Version:**

Vulcanised sealing rings up to 80 bar.

0.5 mm collet Ø clamping range (+ 0.4 / – 0.1).

Suitable for :

ER CP clamping nuts No. 309665 size 25DI.

Note:

Not compatible with other sealing ring systems!

FAHRION system ER clamping nuts type CP and sealing rings type HP **do not fit on to other systems!**

· **Sealing rings in 0.5 mm increments on request.**

· **Sealing rings for No. 309665 DI40 on request.**

External Ø D: 20.2 mm

Height L: 2 mm

Technical description

Clamping Ø	16 mm
Series	Centro P
for type	DI25
External Ø D	20.2 mm

Height L

2 mm