



## Digital caliper IP67 i-wi, Measuring range: 200mm



### Order data

Order number	412738 200
GTIN	4059192002503
Item class	43A

### Description

#### Version:

Very large LCD display with 11 mm character height. Integral i-wi wireless data interface. Resistant to dust and moisture. Service life approx. 3 years.

#### Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Supplied with:

1 battery No. 081560 size CR2032

#### Optional extras:

i-wi radio receiver No. 498912.

Packaging: sturdy box

Standard: ISO 13385

Reversible reading: mm / inch

Depth gauge: rectangular 3.7×1.3

IP Index of Protection: IP 67

Wireless application: Manufacturer's software

Measured value saving: MAHR reference-lock system

Scale divisions: 0.01 mm

Scale divisions: 0.0005 in

Jaw length: 50 mm

Wireless application: Manufacturer's software

### Technical description

Reversible reading	mm / inch
--------------------	-----------

Depth gauge available	yes
Digit height LCD display	11 mm
Jaw length	50 mm
Working time	approx. 3 years
Depth gauge	rectangular 3.7×1.3
Calibration	A1
Standard	ISO 13385
Scale divisions	0.01 mm
Scale divisions	0.0005 in
Measuring range	0 - 200 mm
Measured value saving	MAHR reference-lock system
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
IP Index of Protection	IP 67
Power supply	Battery-powered
Wireless application	Manufacturer's software
Measurement deviation E MPE	± 0.03 mm
Interface	MAHR i-wi radio system
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

## Services

Calibration Calipers / depth gauges maximum measuring range 200 mm	011030 200
Labelling laser-etched Type	018940
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	011050 200

Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200

### Accessories

Radio receivers for Mahr i-wi Type STICK	498912 STICK
Button cell / special battery Battery type CR2032	081560 CR2032