



Digital caliper IP67 i-wi, Measuring range: 200mm



Order data

Order number	412738 200
GTIN	4059192002503
Item class	43A

Description

Version:

Very large LCD display with 11 mm character height. Integral i-wi wireless data interface. Resistant to dust and moisture. The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons. Service life approx. 3 years.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032

Optional extras:

i-wi radio receiver No. 498912.

Technical description

Reversible reading	mm / inch
Depth gauge available	yes
Digit height LCD display	11 mm
Jaw length	50 mm
Working time	approx. 3 years
Depth gauge	rectangular 3.7×1.3
Calibration	A1

Standard	ISO 13385
Scale divisions	0.01 mm
Scale divisions	0.0005 in
Measuring range	0 - 200 mm
Measured value saving	MAHR reference-lock system
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
IP Index of Protection	IP 67
Power supply	Battery-powered
Wireless application	Manufacturer's software
Measurement deviation E MPE	± 0.03 mm
Interface	MAHR i-wi radio system
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200

Accessories

Radio receivers for Mahr i-wi Type STICK	498912 STICK
Button cell / special battery Battery type CR2032	081560 CR2032