


**Scroll jaw set, 4 pieces, soft, for chuck type: 125mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 314700 125    |
| GTIN         | 4019208034478 |
| Item class   | 33R           |

**Description****Material:**

16 MnCr5

**Suitable for:**

Four-jaw lathe chucks No. 312505; 312705.

**Note:**

- Jaws can generally be renewed in the chuck as long as the guide in the body is not worn out.
- Top, turning, and drilling jaws bought subsequently must be ground in the chuck for radial and axial run-out.

**Technical description**

|                          |                                    |
|--------------------------|------------------------------------|
| Width B                  | 18 mm                              |
| Length L                 | 52 mm                              |
| for chuck type           | 125 mm                             |
| Height H                 | 41.5 mm                            |
| suitable for colour code | Röhm geared scroll chucks and jaws |
| Type of product          | Gear scroll chuck jaws             |

