

 Mahr**Digital caliper IP67 i-wi, Measuring range: 300mm****Order data**

Order number	412738 300
GTIN	4059192002527
Item class	43A

Description**Version:**

Very large LCD display with 11 mm character height. Integral i-wi wireless data interface. Resistant to dust and moisture. The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons. Service life approx. 3 years. Without depth gauge.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032

Optional extras:

i-wi radio receiver No. 498912.

Technical description

Jaw length	64 mm
Reversible reading	mm / inch
Working time	approx. 3 years
Calibration	A1
Standard	ISO 13385
Digit height LCD display	11 mm

Scale divisions	0.01 mm
Scale divisions	0.0005 in
Measuring range	0 - 300 mm
Measured value saving	MAHR reference-lock system
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
IP Index of Protection	IP 67
Power supply	Battery-powered
Wireless application	Manufacturer's software
Measurement deviation E MPE	± 0.04 mm
Interface	MAHR i-wi radio system
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 300 mm	021000 300
DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm	021010 300

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Radio receivers for Mahr i-wi Type STICK	498912 STICK
Plastic case Type MS300	412470 MS300