



TESA TWIN-CAL digital caliper, Measuring range: 150mm



Order data

Order number	412766 150
GTIN	7630041106176
Item class	45A

Description

Version:

Large high-contrast display with 11 mm character height. More than 12,000 operating hours, automatic standby after 10 min and automatic shutdown after 2 h. ABS measurement mode, integral TLC port for data transmission. Without thumb roller.

Application:

External, internal, step and depth measurements.

Supplied with:

1 battery No. 081560 CR2032.

Optional extras:

Data cable No. 498918, radio No. 498921 size BT.

Technical description

Reversible reading	mm / inch
Auto switch-off	yes
Working time	12000 h
Depth gauge available	yes
Jaw length	40 mm
Standard	ISO 13385
Calibration	A1
Digit height LCD display	11 mm

Depth gauge	rectangular 3.7×1.3
Automatic stand-by circuit.	yes
Scale divisions	0.01 mm
Scale divisions	0.0005 in
Measuring range	0 - 150 mm
Measured value saving	Once-off setting of the zero position
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Battery type	Button cell
Power supply	Battery-powered
International size	CR2032
Measurement deviation E MPE	±0.03 mm
Interface	TESA Link Connector TLC
Interface	USB interface
Interface	Digimatic interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200
Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200

Accessories

Data cable TLC, 2 m Type USB	498918 USB
------------------------------	------------

Receiver / USB keyboard interface Type	498965
Button cell / special battery Battery type CR2032	081560 CR2032
Data cable TLC, 2 m Type D	498918 D
Multi-receiver / USB keyboard interface Type	498975