

 Mahr

## Workshop caliper in lightweight design, Measuring range: 800mm



### Order data

Order number	412750 800
GTIN	2050001060303
Item class	43A

### Description

#### Version:

**Lightweight workshop caliper** with measuring tips and Vee guides.

#### Parallax-free reading.

Aluminium beam and slide. 50% weight advantage. Wear and scratch resistant with hard anodised surface 1100 HV (similar to ceramic).

Jaws and tips stainless, hardened and ground. Vernier with high-contrast scale and internal scale. Slide runs easily and precisely.

### Technical description

Calibration	A1
Type of reading parts	satin chrome-plated
Weight	1.6 kg
Jaw length	150 mm
Locking	Locking screw at top
Scale divisions	0.02 mm
Measuring range	0 - 800 mm
Type of measurement face	hardened
Internal jaw $\varnothing$	20 mm
Surface	hard anodised

Graduation	1/50 mm
Error limit	0.07 mm
Packaging	sturdy box
Standard	Manufacturer's standard
Measurement technology	analogue
Type of product	Workshop calipers

### Services

CalibrationCalipers / depth gauges maximum measuring range 1000 mm	021000 1000
DAkkS calibrationCalipers / depth gauges maximum measuring range 1000 mm	021010 1000