

 Mahr

Workshop caliper in lightweight design, Measuring range: 1000mm



Order data

| | |
|--------------|---------------|
| Order number | 412750 1000 |
| GTIN | 2050001060310 |
| Item class | 43A |

Description

Version:

Lightweight workshop caliper with measuring tips and Vee guides.

Parallax-free reading.

Aluminium beam and slide. 50% weight advantage. Wear and scratch resistant with hard anodised surface 1100 HV (similar to ceramic).

Jaws and tips stainless, hardened and ground. Vernier with high-contrast scale and internal scale.

Slide runs easily and precisely.

Standard: Manufacturer's standard

Packaging: sturdy box

Calibration: A1

Scale divisions: 0.02 mm

Graduation: 1/50 mm

Error limit: 0.08 mm

Jaw length: 150 mm

Internal jaw \varnothing : 20 mm

Weight: 1.75 kg

Technical description

| | |
|-----------------------|----------------------|
| Type of reading parts | satin chrome-plated |
| Scale divisions | 0.02 mm |
| Locking | Locking screw at top |
| Weight | 1.75 kg |

| | |
|----------------------------|-------------------------|
| Type of measurement face | hardened |
| Measuring range | 0 - 1000 mm |
| Calibration | A1 |
| Internal jaw \varnothing | 20 mm |
| Surface | hard anodised |
| Jaw length | 150 mm |
| Graduation | 1/50 mm |
| Error limit | 0.08 mm |
| Packaging | sturdy box |
| Standard | Manufacturer's standard |
| Measurement technology | analogue |
| Type of product | Workshop calipers |

Services

| | |
|---|-------------|
| Calibration Calipers / depth gauges maximum measuring range 1000 mm | 011030 1000 |
| Labelling laser-etched Type | 018940 |
| DAkkS calibration Calipers / depth gauges maximum measuring range 1000 mm | 011050 1000 |
| Calibration Calipers / depth gauges maximum measuring range 1000 mm | 021000 1000 |
| DAkkS calibration Calipers / depth gauges maximum measuring range 1000 mm | 021010 1000 |