

 Mahr**Workshop caliper in lightweight design, Measuring range: 1000mm****Order data**

Order number	412750 1000
GTIN	2050001060310
Item class	43A

**Description****Version:**

**Lightweight workshop caliper** with measuring tips and Vee guides.

**Parallax-free reading.**

Aluminium beam and slide. 50% weight advantage. Wear and scratch resistant with hard anodised surface 1100 HV (similar to ceramic).

Jaws and tips stainless, hardened and ground. Vernier with high-contrast scale and internal scale. Slide runs easily and precisely.

**Technical description**

Type of reading parts	satin chrome-plated
Scale divisions	0.02 mm
Locking	Locking screw at top
Weight	1.75 kg
Type of measurement face	hardened
Measuring range	0 - 1000 mm
Calibration	A1
Internal jaw $\varnothing$	20 mm
Surface	hard anodised
Jaw length	150 mm

Graduation	1/50 mm
Error limit	0.08 mm
Packaging	sturdy box
Standard	Manufacturer's standard
Measurement technology	analogue
Type of product	Workshop calipers

### Services

CalibrationCalipers / depth gauges maximum measuring range 1000 mm	021000 1000
DAkkS calibrationCalipers / depth gauges maximum measuring range 1000 mm	021010 1000