

**TESA TWIN-CAL digital caliper, Measuring range: 300mm****Order data**

Order number	412766 300
GTIN	7630041106169
Item class	45A

Description**Version:**

Large high-contrast display with 11 mm character height. More than 12,000 operating hours, automatic standby after 10 min and automatic shutdown after 2 h. ABS measurement mode, integral TLC port for data transmission. With thumb roller.

Application:

External, internal, step and depth measurements.

Supplied with:

1 battery No. 081560 CR2032.

Optional extras:

Data cable No. 498918, radio No. 498921 size BT.

Technical description

Digit height LCD display	11 mm
Automatic stand-by circuit.	yes
Standard	ISO 13385
Depth gauge	rectangular 3.7×1.3
Auto switch-off	yes
Reversible reading	mm / inch
Drive roller	yes
Working time	12000 h
Calibration	A1

Depth gauge available	yes
Jaw length	64 mm
Scale divisions	0.01 mm
Scale divisions	0.0005 in
Measuring range	0 - 300 mm
Measured value saving	Once-off setting of the zero position
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
Battery type	Button cell
Power supply	Battery-powered
International size	CR2032
Measurement deviation E MPE	±0.03 mm
Interface	TESA Link Connector TLC
Interface	USB interface
Interface	Digimatic interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 300 mm	021000 300
DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm	021010 300

Accessories

Data cable TLC, 2 m Type D	498918 D
----------------------------	----------

Receiver / USB keyboard interface Type	498965
Button cell / special battery Battery type CR2032	081560 CR2032
Data cable TLC, 2 m Type USB	498918 USB
Plastic case Type MS300	412470 MS300
Multi-receiver / USB keyboard interface Type	498975