

 Mahr**Workshop caliper in lightweight design, Measuring range: 1500mm****Order data**

Order number	412750 1500
GTIN	2050001060327
Item class	43A

**Description****Version:**

**Lightweight workshop caliper** with measuring tips and Vee guides.

**Parallax-free reading.**

Aluminium beam and slide. 50% weight advantage. Wear and scratch resistant with hard anodised surface 1100 HV (similar to ceramic).

Jaws and tips stainless, hardened and ground. Vernier with high-contrast scale and internal scale.

Slide runs easily and precisely.

Standard: Manufacturer's standard

Calibration: A1

Scale divisions: 0.02 mm

Graduation: 1/20 mm

Error limit: 0.16 mm

Jaw length: 150 mm

Internal jaw Ø: 30 mm

Weight: 2.1 kg

**Technical description**

Type of reading parts	satin chrome-plated
Locking	Locking screw at top
Scale divisions	0.02 mm
Weight	2.1 kg
Surface	hard anodised

Internal jaw Ø	30 mm
Jaw length	150 mm
Measuring range	0 - 1500 mm
Type of measurement face	hardened
Calibration	A1
Graduation	1/20 mm
Error limit	0.16 mm
Standard	Manufacturer's standard
Measurement technology	analogue
Type of product	Workshop calipers

## Services

Calibration Calipers / depth gauges maximum measuring range 2000 mm	011030 2000
Labelling laser-etched Type	018940
Calibration Calipers / depth gauges maximum measuring range 2000 mm	021000 2000