



Digital caliper IP67 with data output, Measuring range: 300mm



Order data

Order number	412742 300
GTIN	4059192002268
Item class	43A

Description

Version:

Clearly legible, high-contrast LCD display. Inductive, waterproof measuring system. The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons. The measuring faces are precision-lapped. Without depth gauge.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032

Optional extras:

Data cable No. 498940.

Technical description

Guidance	Raised slides
Calibration	A1
Auto switch-off	yes
Working time	approx. 3 years
Jaw length	64 mm
Reversible reading	mm / inch
Standard	ISO 13385

Scale divisions	0.01 mm
Scale divisions	0.0005 in
Measuring range	0 - 300 mm
Measured value saving	MAHR reference-lock system
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
IP Index of Protection	IP 67
Power supply	Battery-powered
Measurement deviation E MPE	± 0.04 mm
Interface	RS232C interface
Interface	USB interface
Interface	Digimatic interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm	021010 300
CalibrationCalipers / depth gauges maximum measuring range 300 mm	021000 300

Accessories

Connection cablesimplex with data key Type R2	498940 R2
Connection cablesimplex with data key Type USB2	498940 USB2
Connection cablesimplex with data key Type D2	498940 D2
Battery compartment cover	412235

Button cell / special battery Battery type CR2032	081560 CR2032
Plastic case Type MS300	412470 MS300