



Workshop caliper in lightweight design, Measuring range: 2000mm



Order data

Order number	412750 2000
GTIN	
Item class	43A

Description

Version:

Lightweight workshop caliper with measuring tips and Vee guides.

Parallax-free reading.

Aluminium beam and slide. 50% weight advantage. Wear and scratch resistant with hard anodised surface 1100 HV (similar to ceramic).

Jaws and tips stainless, hardened and ground. Vernier with high-contrast scale and internal scale. Slide runs easily and precisely.

Technical description

Surface	hard anodised
Calibration	A1
Scale divisions	0.02 mm
Locking	Locking screw at top
Type of measurement face	hardened
Measuring range	0 - 2000 mm
Jaw length	150 mm
Type of reading parts	satin chrome-plated
Internal jaw \varnothing	30 mm
Weight	2.5 kg

Graduation	1/20 mm
Error limit	0.16 mm
Standard	Manufacturer's standard
Measurement technology	analogue
Type of product	Workshop calipers

Services

Calibration Calipers / depth gauges maximum measuring range 2000 mm	021000 2000
---	-------------