

**Digital caliper TWIN-CAL IP67, Measuring range: 300mm****Order data**

Order number	412786 300
GTIN	7630041106329
Item class	45A

Description**Version:**

Large high-contrast display with 11 mm character height. More than 12,000 hours service life, automatic standby after 10 minutes and automatic shutdown after 2 hours. ABS measurement mode, integral TLC port for data transmission. All-round protection against liquids. Casing with steel protection plate and "Soft Touch" surface. With thumb roller.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

External, internal, step and depth measurements.

Supplied with:

1 battery No. 081560 size CR2032

Optional extras:

Data cable No. 498918, radio No. 498921 size BT.

Technical description

Auto switch-off	yes
Jaw length	64 mm
Working time	12000 h
Digit height LCD display	11 mm
Drive roller	yes
Depth gauge	rectangular 3.7×1.3

Calibration	A1
Automatic stand-by circuit.	yes
Depth gauge available	yes
Reversible reading	mm / inch
Standard	ISO 13385
Scale divisions	0.01 mm
Scale divisions	0.0005 in
Measuring range	0 - 300 mm
Measured value saving	once-off setting of the zero position
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
Battery type	Button cell
IP Index of Protection	IP 67
Power supply	Battery-powered
International size	CR2032
Measurement deviation E MPE	± 0.03 mm
Interface	Digimatic interface
Interface	USB interface
Interface	TESA Link Connector TLC
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

DAkKS calibration Calipers / depth gauges maximum measuring range 300 mm	021010 300
Calibration Calipers / depth gauges maximum measuring range 300 mm	021000 300

Accessories

Plastic case Type MS300	412470 MS300
Data cable TLC, 2 m Type D	498918 D
Button cell / special battery Battery type CR2032	081560 CR2032
Data cable TLC, 2 m Type USB	498918 USB