



Laser spirit level, Length: 240mm



Order data

Order number	468460 240
GTIN	4007368096207
Item class	460

Description

Version:

Robust, easy to use aluminium housing with 3 point lasers at angles of 90° to each other. The accuracy of the vials and laser in relation to the measuring face is 0.2 mm / m. Four powerful magnets are inset in the base. Contact surface with laser reference edge (edge = centre of laser).

Application:

For quick alignment, marking, and levelling.

Supplied with:

Alignment plate for uneven ground. 3 batteries No. 081561 size LR3.

Technical description

Width	25 mm
Length	240 mm
Laser class	2
Threaded socket for stand	1/4 UNC in
Range	30 m
Height	44 mm
Article no of the battery / rechargeable battery fitted	081561 LR3
Number of batteries contained	3

Error limit	0.2 mm/m
Power supply	Battery-powered
Measurement technology	analogue
Type of product	Spirit level

Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------