



Digital caliper IP67 with data output, Measuring range: 150 mm



Order data

Order number	412744 150
GTIN	4059192002220
Item class	43A

Description

Version:

Clearly legible, high-contrast LCD display. Waterproof inductive measurement system with reference-lock function. The measuring faces are precision lapped.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032

Optional extras:

Data cable No. 498940.

Packaging: sturdy box

Standard: DIN 862

Reversible reading: mm / inch

Depth gauge: flat

IP Index of Protection: IP 67

Measured value saving: MAHR reference-lock system

Calibration: A1

Scale divisions: 0.01 mm

Scale divisions: 0.0005 in

Error limit: 0.03 mm

Jaw length: 40 mm

Technical description

Working time	approx. 3 years
--------------	-----------------

Data sheet

Guidance	Raised slides
Auto switch-off	yes
Reversible reading	mm / inch
Depth gauge available	yes
Standard	DIN 862
Depth gauge	flat
Jaw length	40 mm
Calibration	A1
Scale divisions	0.01 mm
Scale divisions	0.0005 in
Error limit	0.03 mm
Measuring range	0 - 150 mm
Measured value saving	MAHR reference-lock system
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
IP Index of Protection	IP 67
Power supply	Battery-powered

Services

Calibration Calipers / depth gauges maximum measuring range 200 mm	011030 200
Labelling laser-etched Type	018940
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	011050 200
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200
Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Connecting cable Type R2	498940 R2
Plastic case Type MS150	412468 MS150
Connecting cable Type D2	498940 D2
Battery compartment cover	412235
Connecting cable Type USB2	498940 USB2
Plastic case Type MS150	412470 MS150