



Vernier caliper, Measuring range: 200mm



Order data

Order number	415184 200
GTIN	4045197479815
Item class	41Z

Description

Version:

Reading parts **anti-glare satin chrome-plated** with sharp contrast, jet black scale. Lapped measuring faces. Offset and rounded jaw ends for internal measurements.

Technical description

Measuring range	0 - 200 mm
Calibration	A1
Type of reading parts	satin chrome-plated
Scale divisions	0.05 mm
Jaw length	60 mm
Internal jaw \varnothing	10 mm
Graduation	1/20 mm
Packaging	sturdy box
Standard	ISO 13385
Measurement deviation E MPE	± 0.05 mm
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened

Type of product

Workshop calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm

021000 200

DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm

021010 200