

HOLEX**Workshop vernier caliper with mm and inch graduations, Measuring range: 300mm****Order data**

Order number	415100 300
GTIN	4045197203151
Item class	41Z

Description**Version:**

Chamfered measuring tips for measurements to the root of threads and in narrow grooves. Offset and rounded jaw ends for internal measurements. High-contrast scale. With locking screw. Up to size 300 through hardened, from size 500 measuring faces hardened.

Technical description

Jaw length	90 mm
Measuring range	0 - 300 mm
Internal jaw \varnothing	10 mm
Calibration	A1
Locking	Locking screw at top
Reversible reading	mm / inch
Graduation	1/128 in
Graduation	1/20 mm
Packaging	sturdy box
Standard	ISO 13385
Measurement deviation E MPE	± 0.08 mm

Vernier graduations mm/inch	yes
Measurement technology	analogue
Material	Stainless steel, INOX
Type of product	Workshop calipers

Services

DAkkS calibration Calipers / depth gauges maximum measuring range 300 mm	021010 300
Calibration Calipers / depth gauges maximum measuring range 300 mm	021000 300

Accessories

Plastic case Type MS300	412470 MS300
-------------------------	--------------