



## Digital caliper with pointed measurement jaws and rod type depth gauge, Measuring range: 150mm



### Order data

Order number	412753 150
GTIN	4059192002329
Item class	43A

### Description

#### Version:

Clearly legible, high-contrast LCD display. Inductive, waterproof measuring system. The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons.

#### Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Supplied with:

1 battery No. 081560 size CR2032

#### Optional extras:

Data cable No. 498940.

### Technical description

Depth gauge available	yes
Depth gauge	Ø 1.6
Calibration	A1
Jaw length	40 mm
Reversible reading	mm / inch
Standard	Manufacturer's standard

Scale divisions	0.01 mm
Scale divisions	0.0005 in
Error limit	0.03 mm
Measuring range	0 - 150 mm
Measured value saving	MAHR reference-lock system
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
IP Index of Protection	IP 67
Power supply	Battery-powered
Interface	USB interface
Interface	Digimatic interface
Interface	RS232 interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

## Services

DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200
CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200

## Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Connection cablesimplex with data key Type R2	498940 R2
Connection cablesimplex with data key Type D2	498940 D2
Battery compartment cover	412235

Connection cablesimplex with data key Type USB2

498940 USB2