



## Electronic light metal spirit level, Length: 800mm



### Order data

Order number	467554 800
GTIN	4005069198282
Item class	46M

### Description

#### Version:

Exceptionally robust aluminium rectangular profile with shock-absorbing end caps. Two optimally legible digital displays in every operating situation – illuminated at the push of a button. Dustproof and waterproof.

Display modes: °, %, mm/m, in/ft – decimal and as fractions. Keyboard lock. Acoustic targeting with two different audible signals. Reference value freely selectable. Warning if the spirit level is tipped in the second axis. **Self-calibrating in steps of 90°**. Up to 400 hours operation on a single battery charge.

#### Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Supplied with:

Including batteries No. 081551 LR6.

Including transport bag.

### Technical description

Length	800 mm
Graduations can be switched over	0.05 / 0.1 degrees
Article no of the battery / rechargeable battery fitted	081557 LR6
Number of batteries contained	2
Error limit of electronics module	0.05 (0°; 90°); 0.2 (1°-89°) degrees
IP Index of Protection	IP 67
Power supply	Battery-powered

Error limit in normal position and for measurement reversal	0.5 mm/m
Display mode	°, %, mm/m, in/ft – decimal and as fractions
Battery life approx.	150 h
Measurement technology	digital
Calibration	H2
Type of product	Spirit level

### Services

Calibration Engineer's level / electronic clinometer Accuracy 0,10 mm/m	026620 0,10
--	-------------