



## Workshop vernier caliper in lightweight design, Measuring range: 900mm



### Order data

Order number	412770 900
GTIN	4067263118985
Item class	42A

### Description

#### Version:

Workshop vernier caliper in **lightweight design**. **Parallax-free readings** with the highest contrast due to white scaling on black surface. Optimum guidance and sliding characteristics due to internal double Vee guides. Exchangeable measuring jaws made of hardened stainless steel, precision ground.

#### Optional extras:

Measuring jaws of 125 mm, 150 mm.

### Technical description

Packaging	sturdy box
Calibration	A1
Weight	0.8 kg
Jaw length	90 mm
Internal jaw $\varnothing$	10 mm
Measuring range	0 - 900 mm
Vernier	1/20
Error limit	0.11 mm
Standard	Works standard
Measurement technology	analogue

all parts	hardened
Type of product	Workshop calipers

**Services**

DAkkS calibrationCalipers / depth gauges maximum measuring range 1000 mm	021010 1000
CalibrationCalipers / depth gauges maximum measuring range 1000 mm	021000 1000