

HOLEX**Workshop vernier caliper with mm and inch graduations, Measuring range: 500mm****Order data**

Order number	415100 500
GTIN	4045197203168
Item class	41Z

Description**Version:**

Chamfered measuring tips for measurements to the root of threads and in narrow grooves. Offset and rounded jaw ends for internal measurements. High-contrast scale. With locking screw. Up to size 300 through hardened, from size 500 measuring faces hardened.

Technical description

Reversible reading	mm / inch
Jaw length	150 mm
Internal jaw \varnothing	20 mm
Calibration	A1
Measuring range	0 - 500 mm
Type of measurement face	hardened
Locking	Locking screw at top
Graduation	1/128 in
Graduation	1/20 mm
Packaging	sturdy box
Standard	ISO 13385

Measurement deviation E MPE	± 0.1 mm
Vernier graduations mm/inch	yes
Measurement technology	analogue
Material	Stainless steel, INOX
Type of product	Workshop calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 500 mm	021000 500
DAkkS calibrationCalipers / depth gauges maximum measuring range 500 mm	021010 500