

**Vernier caliper, Measuring range: 300mm****Order data**

Order number	415184 300
GTIN	4045197479822
Item class	41Z

Description**Version:**

Reading parts **anti-glare satin chrome-plated** with sharp contrast, jet black scale. Lapped measuring faces. Offset and rounded jaw ends for internal measurements.

Technical description

Type of reading parts	satin chrome-plated
Calibration	A1
Internal jaw \varnothing	10 mm
Scale divisions	0.05 mm
Measuring range	0 - 300 mm
Jaw length	90 mm
Graduation	1/20 mm
Packaging	sturdy box
Standard	ISO 13385
Measurement deviation E MPE	± 0.08 mm
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened

Type of product

Workshop calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 300 mm

021000 300

DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm

021010 300