



## Digital caliper with inwards-facing measuring jaws, Measuring range: 150mm



### Order data

Order number	412754 150
GTIN	4059192002350
Item class	43A

### Description

#### Version:

Clearly legible, high-contrast LCD display. Inductive, waterproof measuring system. The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons.

#### Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Supplied with:

1 battery No. 081560 size CR2032

#### Optional extras:

Data cable No. 498940.

### Technical description

Standard	Manufacturer's standard
Calibration	A1
Reversible reading	mm / inch
Jaw length	40 mm
Scale divisions	0.01 mm
Scale divisions	0.0005 in
Error limit	0.03 mm

## Data sheet

Measuring range	0 - 150 mm
Measured value saving	MAHR reference-lock system
#Number of batteries contained	1
#Article no of the battery / rechargeable battery fitted	081560 CR2032
IP Index of Protection	IP 67
Power supply	Battery-powered
Interface	USB interface
Interface	Digimatic interface
Interface	RS232 interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

### Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/412754-150>