

STIEFELMAYER

**Shaft spirit level, Base Length×Accuracy: 300/2mm**

**Order data**

Order number	468800 300/2
GTIN	4028126003572
Item class	46R

**Description**
**Version:**

Sturdy housing of high quality special casting; hammer finish. Vee and flat base with precision-ground contact surfaces in the angle (important for marking out, aligning, etc.). All measuring faces are exactly parallel to the axis of the vial. One longitudinal and one transverse vial each of glass. With insulated handles on the housing and protective glass over the vials.

**Application:**

For aligning surfaces, shafts, machines etc.

**Standard:**

**DIN 877**

**Accuracy:**

**1** = with very high sensitivity longitudinal vial **0.02 mm/m.**

**2** = with high sensitivity longitudinal vial **0.1 mm/m.**

**4** = with normal sensitivity longitudinal vial **0.4 mm/m.**

**Technical description**

Accuracy class	2
Scale divisions	0.1 mm/m
Sole width	50 mm
Sole length	300 mm
Standard	DIN 877
Packaging	sturdy box

Calibration	H2
Type of product	Spirit level
<b>Services</b>	
Calibration Engineer's level / electronic clinometer Accuracy 0,10 mm/m	026620 0,10