



Digital caliper with outwards-facing measuring jaws, Measuring range: 150mm



Order data

Order number	412755 150
GTIN	4059192002367
Item class	43A

Description

Version:

Clearly legible, high-contrast LCD display. Waterproof inductive measurement system with reference-lock function.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032

Optional extras:

Data cable No. 498940.

Packaging: sturdy box

Standard: Manufacturer's standard

Reversible reading: mm / inch

IP Index of Protection: IP 67

Measured value saving: MAHR reference-lock system

Calibration: A1

Scale divisions: 0.01 mm

Scale divisions: 0.0005 in

Error limit: 0.03 mm

Jaw length: 40 mm

Technical description

Reversible reading	mm / inch
--------------------	-----------

Jaw length	40 mm
Standard	Manufacturer's standard
Type of caliper jaws	angled outwards
Calibration	A1
Scale divisions	0.01 mm
Scale divisions	0.0005 in
Error limit	0.03 mm
Measuring range	0 - 150 mm
Measured value saving	MAHR reference-lock system
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
IP Index of Protection	IP 67
Power supply	Battery-powered
Interface	USB interface
Interface	Digimatic interface
Interface	RS232 interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

Calibration Calipers / depth gauges maximum measuring range 200 mm	011030 200
Labelling laser-etched Type	018940
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	011050 200
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200

Calibration Calipers / depth gauges maximum measuring range 200 mm

021000 200

Accessories

Connecting cable Type D2

498940 D2

Battery compartment cover

412235

Connecting cable Type USB2

498940 USB2

Connecting cable Type R2

498940 R2

Button cell / special battery Battery type CR2032

081560 CR2032