

 Mahr**Digital caliper IP67 i-wi, Measuring range: 150mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 412738 150    |
| GTIN         | 4059192002480 |
| Item class   | 43A           |

**Description****Version:**

Very large LCD display with 11 mm character height. Integral i-wi wireless data interface. Resistant to dust and moisture. The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons. Service life approx. 3 years.

**Function:**

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

1 battery No. 081560 size CR2032

**Optional extras:**

i-wi radio receiver No. 498912.

**Technical description**

|                          |                     |
|--------------------------|---------------------|
| Working time             | approx. 3 years     |
| Depth gauge              | rectangular 3.7×1.3 |
| Depth gauge available    | yes                 |
| Reversible reading       | mm / inch           |
| Digit height LCD display | 11 mm               |
| Calibration              | A1                  |
| Jaw length               | 40 mm               |

|   |                            |
|---|----------------------------|
| Standard  | ISO 13385                  |
| Scale divisions   | 0.01 mm                    |
| Scale divisions   | 0.0005 in                  |
| Measuring range   | 0 - 150 mm                 |
| Measured value saving                                   | MAHR reference-lock system |
| Article no of the battery / rechargeable battery fitted | 081560 CR2032              |
| Number of batteries contained                           | 1                          |
| IP Index of Protection                                  | IP 67                      |
| Power supply  | Battery-powered            |
| Wireless application                                    | Manufacturer's software    |
| Measurement deviation E MPE                             | $\pm 0.03$ mm              |
| Interface   | MAHR i-wi radio system     |
| Measurement technology                                  | digital                    |
| Material  | Stainless steel, INOX      |
| all parts   | hardened                   |
| Packaging   | sturdy box                 |
| Type of product   | Universal calipers         |

## Services

|  |            |
|--|------------|
| DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm | 021010 200 |
| Calibration Calipers / depth gauges maximum measuring range 200 mm       | 021000 200 |

## Accessories

|   |               |
|---|---------------|
| Radio receivers for Mahr i-wi Type STICK          | 498912 STICK  |
| Button cell / special battery Battery type CR2032 | 081560 CR2032 |