

 Mahr

Workshop caliper in lightweight design, Measuring range: 500mm



Order data

Order number	412750 500
GTIN	2050001060297
Item class	43A

Description

Version:

Lightweight workshop caliper with measuring tips and Vee guides.

Parallax-free reading.

Aluminium beam and slide. 50% weight advantage. Wear and scratch resistant with hard anodised surface 1100 HV (similar to ceramic).

Jaws and tips stainless, hardened and ground. Vernier with high-contrast scale and internal scale. Slide runs easily and precisely.

Technical description

Internal jaw \varnothing	20 mm
Jaw length	150 mm
Weight	1.4 kg
Calibration	A1
Locking	Locking screw at top
Scale divisions	0.02 mm
Type of reading parts	satin chrome-plated
Measuring range	0 - 500 mm
Surface	hard anodised
Type of measurement face	hardened

Graduation	1/50 mm
Error limit	0.05 mm
Packaging	sturdy box
Standard	Manufacturer's standard
Measurement technology	analogue
Type of product	Workshop calipers

Services

DAkkS calibration Calipers / depth gauges maximum measuring range 500 mm	021010 500
Calibration Calipers / depth gauges maximum measuring range 500 mm	021000 500