



High-performance grinding oil concentrate, Contents: 20l



Order data

Order number	084270 20
GTIN	2050000971921
Item class	08J

Description

Version:

Cooling lubricant for **demanding applications, free of hydrochlorous acid, formaldehyde and boric acid**. High-pressure additives prevent displacement of the lubricating film; it remains on the cutting tool in molecular concentrations even under the most severe loading. High performance **grinding concentrate** transparent for a clear view when grinding a wide variety of materials. **Mixing ratio 1: 40** (2.5%).

Advantage:

Improves **tool-life, cutting performance** and **surface quality**. **Chlorine-free** - releases no hazardous vapours, **non-polluting**.

Concentrates **protect against rust**, do not attack paintwork, and are **physiologically harmless**, as well as very **resistant to bacterial contamination**, and kind to the skin.

Note:

Jokisch slide oils and machine bed oils are available on request.

Technical description

Version	Can
Colour	pale yellow

Data sheet

Kinematic viscosity	10 mm ² /s
Shape	liquid
Storage temperature	5 - 40 °C
Contents	20 l
Type of product	Cutting oil / grinding oil
Refractometer value	2