



## Digital caliper TWIN-CAL IP67, Measuring range: 150mm



### Order data

Order number	412786 150
GTIN	7630041106282
Item class	45A

### Description

#### Version:

Large high-contrast display with 11 mm character height. More than 12,000 hours service life, automatic standby after 10 minutes and automatic shutdown after 2 hours. ABS measurement mode, integral TLC port for data transmission. All-round protection against liquids. Casing with steel protection plate and "Soft Touch" surface.

#### Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Application:

External, internal, step and depth measurements.

#### Supplied with:

1 battery No. 081560 size CR2032

#### Optional extras:

Data cable No. 498918, radio No. 498921 size BT.

### Technical description

Standard	ISO 13385
Auto switch-off	yes
Automatic stand-by circuit.	yes
Working time	12000 h
Depth gauge available	yes
Depth gauge	rectangular 3.7×1.3

Reversible reading	mm / inch
Jaw length	40 mm
Calibration	A1
Digit height LCD display	11 mm
Scale divisions	0.01 mm
Scale divisions	0.0005 in
Measuring range	0 - 150 mm
Measured value saving	once-off setting of the zero position
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Battery type	Button cell
IP Index of Protection	IP 67
Power supply	Battery-powered
International size	CR2032
Measurement deviation E MPE	±0.03 mm
Interface	Digimatic interface
Interface	USB interface
Interface	TESA Link Connector TLC
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

## Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200

## Accessories

Data cable TLC, 2 m Type USB	498918 USB
Button cell / special battery Battery type CR2032	081560 CR2032
Data cable TLC, 2 m Type D	498918 D