



Vernier caliper, Measuring range: 800mm



Order data

Order number	415186 800
GTIN	4045197479846
Item class	41Z

Description

Version:

Vernier satin chrome-plated, anti-glare. Measuring faces hardened and ground. **Long jaws for measuring large components and component \varnothing .** With fine adjustment. Offset and rounded jaw ends for internal measurements.

With fine adjustment.

Technical description

Scale divisions	0.05 mm
Weight	3.5 kg
Type of reading parts	satin chrome-plated
Type of measurement face	hardened
Internal jaw \varnothing	20 mm
Measuring range	0 - 800 mm
Calibration	A1
Jaw length	150 mm
Graduation	1/20 mm
Packaging	sturdy box
Standard	ISO 13385
Measurement deviation E MPE	± 0.12 mm

Fine setting	yes
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Type of product	Workshop calipers

Services

DAkkS calibrationCalipers / depth gauges maximum measuring range 1000 mm	021010 1000
CalibrationCalipers / depth gauges maximum measuring range 1000 mm	021000 1000