



Digital clinometer, Type: 3600



Order data

Order number	467560 3600
GTIN	2050001668448
Item class	46R

Description

Version:

- Aluminium frame with precision measurement faces, Vee profile at top.
- Direction arrows in the display facilitate alignment to 0° and 90°.
- Hold function for retaining the measurement result.
- Zero setting in any position.

Supplied with:

Storage case and 1 battery No. 081561 size 6LR61.

Technical description

Graduations	0.01 (0° – 9.99°) / 0.1 (10° – 90°) degrees
Measuring range	360 (4×90°) degrees
Length	153 mm
Flatness tolerance	0.0762 mm
Height	49 mm
Width	31 mm
Article no of the battery / rechargeable battery fitted	081561 6LR61
Number of batteries contained	1

Error limit of electronics module	0.05 (0° – 10°) / 0.1 (80° – 90°) / 0.2 (11° – 79°) degrees
Power supply	Battery-powered
Standard	Manufacturer's standard
Measurement technology	digital
Packaging	sturdy box
Calibration	H2
Type of product	Clinometer

Services

Calibration Engineer's level / electronic clinometer Accuracy 0,02 mm/m	026620 0,02
--	-------------