



## Vernier caliper, Measuring range: 1000mm



### Order data

Order number	415186 1000
GTIN	4045197479853
Item class	41Z

### Description

#### Version:

Vernier satin chrome-plated, anti-glare. Measuring faces hardened and ground. **Long jaws for measuring large components and component Ø.** With fine adjustment. Offset and rounded jaw ends for internal measurements.

With fine adjustment.

### Technical description

Jaw length	200 mm
Internal jaw Ø	20 mm
Weight	3.9 kg
Calibration	A1
Type of measurement face	hardened
Measuring range	0 - 1000 mm
Type of reading parts	satin chrome-plated
Scale divisions	0.05 mm
Graduation	1/20 mm
Packaging	sturdy box
Standard	ISO 13385
Measurement deviation E MPE	± 0.15 mm

Fine setting	yes
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Type of product	Workshop calipers

## Services

CalibrationCalipers / depth gauges maximum measuring range 1000 mm	021000 1000
DAkkS calibrationCalipers / depth gauges maximum measuring range 1000 mm	021010 1000