



Vernier caliper with extra long jaws, Measuring range: 500mm



Order data

| | |
|--------------|---------------|
| Order number | 415188 500 |
| GTIN | 4045197479860 |
| Item class | 41Z |

Description

Version:

Vernier satin chrome-plated, anti-glare. Measuring faces hardened and ground. **Long jaws for measuring large components and component \varnothing .** With fine adjustment. Offset and rounded jaw ends for internal measurements.

With **extra long jaws**, without fine adjustment.

Technical description

| | |
|----------------------------|---------------------------|
| Jaw length | 300 mm |
| Calibration | A1 |
| Type of caliper jaws | extra long measuring jaws |
| Measuring range | 0 - 500 mm |
| Weight | 1.9 kg |
| Internal jaw \varnothing | 20 mm |
| Type of measurement face | hardened |
| Type of reading parts | satin chrome-plated |
| Scale divisions | 0.05 mm |

| | |
|------------------------|-------------------------|
| Graduation | 1/20 mm |
| Error limit | 0.15 mm |
| Packaging | sturdy box |
| Standard | Manufacturer's standard |
| Measurement technology | analogue |
| Material | Stainless steel, INOX |
| all parts | hardened |
| Type of product | Workshop calipers |

Services

| | |
|---|------------|
| CalibrationCalipers / depth gauges maximum measuring range 500 mm | 021000 500 |
| DAkkS calibrationCalipers / depth gauges maximum measuring range 500 mm | 021010 500 |