



## Safety dial indicator, Measuring range / Body Ø: 0,08/58mm



### Order data

Order number	432405 0,08/58
GTIN	4031452101683
Item class	46C

### Description

#### Version:

Dimensions to DIN EN ISO 463, issue June 2006. Precision dial indicators, shockproof, safety dial indicators, shockproof, with overrun. Extremely light, robust construction, dustproof. Clamping shank Ø 8 mm h6.

Highest precision due to combined gear and lever mechanism.

### Technical description

Free stroke	4.5 mm
Body Ø	58 mm
Measuring range	0.08 mm
Gauging force	1.3 - 1.8 N
Calibration	C2
Graduation	0.001 mm
Standard	Manufacturer's standard

Measurement variation MPE (measurement range)	2 µm
Measurement technology	analogue
Packaging	sturdy box
Type of product	dial gauge

## Services

CalibrationDial indicator, analogue 0.001 maximum measuring span 5 mm	023020 5
---	----------