

STIEFELMAYER

Square frame level, Base Length×Accuracy: 150/2mm

Order data

Order number	469200 150/2
GTIN	4028126004371
Item class	46R

Description
Version:

Insulated handles on the housing protect against the effects of body heat.

Sturdy frame of high quality special casting; hammer finish. 3 sides prismatic and flat. 1 side flat, all precision ground. One longitudinal and one transverse vial each of glass. The sensitivity (scale value) of the longitudinal vial is specified on the square.

Application:

For aligning horizontal and vertical faces, shafts etc. and for accurate alignment at a 90° angle.

Standard:
DIN 877
Accuracy:

1 = with very high sensitivity longitudinal vial **0.02 mm/m.**

2 = with high sensitivity longitudinal vial **0.1 mm/m.**

Technical description

Sole length	150 mm
Accuracy class	2
Scale divisions	0.1 mm/m

Sole width	37 mm
Standard	DIN 877
Packaging	sturdy box
Calibration	H1
Type of product	Spirit level

Services

Calibration Square frame level Accuracy 0,10 mm/m	026600 0,10
---	-------------