



Safety dial indicator, Measuring range / Body Ø: 0,8/58mm



Order data

Order number	432405 0,8/58
GTIN	2050001741073
Item class	46C

Description

Version:

Dimensions to DIN EN ISO 463, issue June 2006. Precision dial indicators, shockproof, safety dial indicators, shockproof, with overrun. Extremely light, robust construction, dustproof. Clamping shank Ø 8 mm h6.

Highest precision due to combined gear and lever mechanism.

Technical description

Gauging force	0.8 - 1.2 N
Calibration	C1
Body Ø	58 mm
Graduation	0.01 mm
Measuring range	0.8 mm
Free stroke	7 mm
Standard	DIN 878

Measurement variation MPE (measurement range)	7 μ m
Measurement technology	analogue
Packaging	sturdy box
Type of product	dial gauge

Services

CalibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 3 mm	023000 3
DAkkS calibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 12,5 mm	023010 12,5

Accessories

Dial indicator glass Type 58	432010 58
------------------------------	-----------