

STIEFELMAYER

Shaft spirit level, Base Length×Accuracy: 200/4mm**Order data**

Order number	468800 200/4
GTIN	4028126003350
Item class	46R

Description**Version:**

Sturdy housing of high quality special casting; hammer finish. Vee and flat base with precision-ground contact surfaces in the angle (important for marking out, aligning, etc.). All measuring faces are exactly parallel to the axis of the vial. One longitudinal and one transverse vial each of glass. With insulated handles on the housing and protective glass over the vials.

Application:

For aligning surfaces, shafts, machines etc.

Standard:

DIN 877

Accuracy:

1 = with very high sensitivity longitudinal vial **0.02 mm/m.**

2 = with high sensitivity longitudinal vial **0.1 mm/m.**

4 = with normal sensitivity longitudinal vial **0.4 mm/m.**

Technical description

Sole width	40 mm
Sole length	200 mm
Scale divisions	0.4 mm/m
Accuracy class	4
Standard	DIN 877
Packaging	sturdy box

Calibration	H2
Type of product	Spirit level
Services	
Calibration Engineer's level / electronic clinometer Accuracy 0,40 mm/m	026620 0,40