

STIEFELMAYER

**Square frame level, Base Length×Accuracy: 200/1 mm**

**Order data**

Order number	469200 200/1
GTIN	4045197207203
Item class	46R

**Description**
**Version:**

Insulated handles on the housing protect against the effects of body heat.

Sturdy frame of high quality special casting; hammer finish. 3 sides prismatic and flat. 1 side flat, all precision ground. One longitudinal and one transverse vial each of glass. The sensitivity (scale value) of the longitudinal vial is specified on the square.

**Application:**

For aligning horizontal and vertical faces, shafts etc. and for accurate alignment at a 90° angle.

**Standard:**

**DIN 877**

**Accuracy:**

**1** = with very high sensitivity longitudinal vial **0.02 mm/m**.

**2** = with high sensitivity longitudinal vial **0.1 mm/m**.

**Technical description**

Sole width	41 mm
Scale divisions	0.02 mm/m
Accuracy class	1

Sole length	200 mm
Standard	DIN 877
Packaging	sturdy box
Calibration	H1
Type of product	Spirit level

## Services

CalibrationSquare frame level Accuracy 0,02 mm/m	026600 0,02
--	-------------