

**hanhart**  
1882

## Digital stopwatch



### Order data

|              |               |
|--------------|---------------|
| Order number | 469622        |
| GTIN         | 2050001063380 |
| Item class   | 46R           |

### Description

#### Version:

LCD display with 8 mm characters, 7 digits / + 2 decimal digits for use as an event counter. Display range 9 h, 59 min, 59.99 s. Display graduation value 1/100 s.

#### Function:

- **Start / Stop / Reset.**
- **Cumulative / Split / Dual measurement.**
- **Time of day (2×12 hours a.m. / p.m.).**

#### Supplied with:

Neck cord and 1 battery No. 081560 size 357.

### Technical description

|   |                 |
|---|-----------------|
| Article no of the battery / rechargeable battery fitted | 081560 357      |
| Number of batteries contained                           | 1               |
| Power supply  | Battery-powered |
| Measurement technology                                  | digital         |

|                 |            |
|-----------------|------------|
| Calibration     | N1         |
| Type of product | Stop-watch |

### Services

|                              |          |
|------------------------------|----------|
| CalibrationStop-watch Type U | 029100 U |
|------------------------------|----------|

### Accessories

|  |            |
|--|------------|
| Button cell / special battery Battery type 357 | 081560 357 |
|--|------------|