

HOLEX**Precision dial indicator shock-resistant, Measuring range / Body Ø: 50/58mm****Order data**

Order number	433060 50/58
GTIN	4045197204233
Item class	42C

Description**Version:**

Dimensions to EN ISO 463, issue June 2006 (except size 100/80).

Strong, satin chrome plated brass casing.

Clamping shank Ø 8 mm h6, hardened and ground.

Outer ring of dial face can be rotated to zero the dial.

Central pointer for 1/100 mm reading, small pointer for 1 mm reading.

Optional extras:

Special contact points No. 434900; 434910; 434915.

Technical description

Calibration	C1
Measuring range	50 mm
Body Ø	58 mm
Reading per pointer revolution	1 mm
Gauging force	1 - 2 N

Graduation	0.01 mm
Standard	Manufacturer's standard
Measurement variation MPE (measurement range)	25 µm
Measurement technology	analogue
Type of product	dial gauge

Services

Calibration Dial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 50 mm	023000 50
DAkkS calibration Dial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 100 mm	023010 100

Accessories

Steel contact point Type 11/25	434900 11/25
Steel contact point Type 10	434900 10
Carbide contact point Type 11	434910 11
Carbide contact point Type 2	434910 2
Steel contact point Type 11	434900 11
Steel contact point Type 29/10	434900 29/10
Extension for contact points Length L 20 mm	434920 20
Extension for contact points Length L 70 mm	434920 70
Steel contact point Type 18/1	434900 18/1
Carbide contact point Type 18/1	434910 18/1
Extension for contact points Length L 100 mm	434920 100
Steel contact point Type 24	434900 24
Steel contact point Type 28	434900 28
Steel contact point Type 18/4	434900 18/4
Extension for contact points Length L 10 mm	434920 10
Carbide contact point Type 18/4	434910 18/4

Carbide contact point Type 10	434910 10
Steel contact point Type 12	434900 12
Steel contact point Type 16	434900 16
Extension for contact points Length L 40 mm	434920 40
Steel contact point Type 30/10	434900 30/10
Steel contact point Type 18/3	434900 18/3
Pivoting contact point	434912
Carbide contact point Type 14	434910 14
Extension for contact points Length L 50 mm	434920 50
Steel contact point Type 11/30	434900 11/30
Steel contact point Type 14/20	434900 14/20
Steel contact point Type 14	434900 14
Extension for contact points Length L 90 mm	434920 90
Extension for contact points Length L 30 mm	434920 30
Steel contact point Type 18/5	434900 18/5
Extension for contact points Length L 60 mm	434920 60
Steel contact point Type 11/20	434900 11/20
Steel contact point Type 17	434900 17
Extension for contact points Length L 80 mm	434920 80
Steel contact point Type 18/6	434900 18/6
Steel contact point Type 39	434900 39
Steel contact point Type 29/20	434900 29/20
Carbide contact point Type 16	434910 16
Steel contact point Type 20	434900 20
Ruby contact point Type 2	434915 2
Steel contact point Type 2	434900 2
Steel contact point Type 14/40	434900 14/40
Steel contact point Type 18/2	434900 18/2
Carbide contact point Type 17	434910 17

Steel contact point Type 15	434900 15
Extension for contact points Length L 15 mm	434920 15
Carbide contact point Type 18/2	434910 18/2
Steel contact point Type 11/15	434900 11/15
Steel contact point Type 13	434900 13
Carbide contact point Type 18/3	434910 18/3
Steel contact point Type 14/15	434900 14/15
Carbide contact point Type 18/6	434910 18/6
Steel contact point Type 11/35	434900 11/35
Steel contact point Type 14/30	434900 14/30
Carbide contact point Type 18/5	434910 18/5
Dial indicator glass Type 58	432260 58