

**Quick-release vice for one-hand use, Jaw width A: 135mm****Order data**

Order number	365023 135
GTIN	4045197595430
Item class	32P

Description**Version:**

- **Quick adjustment of the movable jaws.**
- **Jaws through hardened and ground.**
- **Time-consuming cranking not necessary.**
- **Precise clamping due to long flat guide.**
- **Clamping of component with just one hand.**
- **One jaw with horizontal and vertical prismatic profiles for round material, one jaw smooth.**
- **Both jaws are stepped at the top to clamp flat parts.**
- **With two side support faces.**
- **Positive locking.**

Application:

For quick clamping of components on drilling machines and measuring machines.

Material:

Body and movable jaw made of sturdy special cast iron.

Accuracy:

Within **0.03 mm**.

Technical description

Weight	13.5 kg
maximum overall length L ₄	587 mm
Overall height c	80.5 mm

Colour code for suitable accessories	BM vice, grey
Jaw width A	135 mm
Clamping range b	160 mm
Jaw height C	40 mm
Base body width B	138 mm
Base body length a	365 mm
Type of product	Drilling machine vice

Accessories

Backstop Type 2	365028 2
Slide for No. 365023	365025