



Stroke counter with key



Order data

Order number	470100
GTIN	4045197235046
Item class	42H

Description

Version:

Six-digit counter with drive both sides for clockwise actuation. Zeroing can be done from the left or right with an insertable key. Drive shaft projects at both sides; stroke lever can be set to different positions on the shaft. Drive shaft 5 mm \varnothing , numerals height 4.5 mm, hammer finish housing.

Application:

In the machine tool and metal industries on stamping machines, shears, power presses, packing machines, automatic dispensers etc.

Maximum strokes: 500 rpm

Stroke movement minimum – maximum: 32 - 60 degrees

Width: 70 mm

Height: 60 mm

Length: 28 mm

Technical description

Height	60 mm
Stroke movement minimum – maximum	32 - 60 degrees
Width	70 mm
Maximum strokes	500 rpm
Length	28 mm

Height of numerals	4.5 mm
Drive axis Ø	5 mm
Type of product	Stroke counter

Accessories

Zero reset key	470150
----------------	--------