



Infrared thermometer, Type: T2



Order data

Order number	474012 T2
GTIN	4029547011696
Item class	47B

Description

Version:

Quick contact-less measurement over distances.

- **Display: Min / max function**
- **Limit value monitoring with optical and acoustic alarm.**
- **Small and handy with illuminated display.**
- **Quick measurement: 2 measurements/s.**

Real measuring spot marking by **2 laser points.**

Supplied with:

Supplied with test certificate and 1× battery No. 081561 size 6LR61.

Optional extras:

Protective case No. 474029.

Technical description

Error limit (0.1 to 400 °C)	± 1.5 or ± 1.5 % of the measured value °C
Optics	12 : 1

Error limit (-30 to 0 °C)	±2 or ±2 % of the measured value °C
Weight	200 g
Length	75 mm
Measuring range	-30 - 400 °C
Emission level adjustable	0.1 - 1
Width	38 mm
Infra-red resolution	0.1 °C
Height	190 mm
Article no of the battery / rechargeable battery fitted	081561 6LR61
Number of batteries contained	1
Power supply	Battery-powered
Calibration	I5
Type of product	Temperature measuring device

Services

CalibrationInfra-red temperature measuring tool Type A	027600 A
--	----------

Accessories

Temperature sensor Type K Type OF	474120 OF
Temperature sensor Type K Type EF	474120 EF
Leather protective cover	474029