

**Voltage tester, Device type: LCD****Order data**

Order number	473120 LCD
GTIN	4045197554260
Item class	42I

**Description****Version:**

Two-component plastic casing with 2 test prods. Integral LED lamp, test prod mounting for one-hand operation, auto-test for checking its operation. Automatic selection of measurement range.

**Function:**

IP64: Protected against splashed water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

**Application:**

For professional multi-stage voltage, continuity, and polarity testing.

**Standard:**

**IEC / DIN EN 61243-3; GS TÜV Rheinland.**

**Supplied with:**

2 batteries No. 081551 size LR3, protective caps.

IP Index of Protection: IP 64

Calibration: I1

Display range AC: 6 - 400 V

Display range DC: 6 - 690 V

Display: LCD

Display backlit: yes

Three phase sequence testing: yes

Continuity testing: acoustic / LCD

## Technical description

Three phase sequence testing	yes
Display range DC	6 - 690 V
Illumination of probe points	yes
Overvoltage category	CAT III 1000 V; CAT IV 600 V
Display	LCD
Display range AC	6 - 400 V
Manufacturer's designation	LCD
Continuity testing	acoustic / LCD
Display backlit	yes
IP Index of Protection	IP 64
Calibration	I1
Safety certificate	GS TÜV Rheinland
Number of batteries contained	2
Article no of the battery / rechargeable battery fitted	081551 LR3
Power supply	Battery-powered
Power supply	2x No. 081551 size LR3
Type of product	Voltage tester

## Services

Labelling laser-etched Type	018940
Calibration Voltage tester	017870
Calibration Voltage tester Type S	027120 S
DAkkS calibration Voltage tester Type S	027160 S

## Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------

Alkaline-manganese batteries International size LR3

081556 LR3