

BENNING**Phase and phase sequence tester Tritest Easy, Type:****Order data**

Order number	473280
GTIN	4014651200517
Item class	47A

Description**Version:**

Non-contact test device, automatic shut-down. Flashing frequency and audio frequency increase as the detected voltage increases. For quick and easy phase testing at sockets, junction boxes, switches and lamps. Locates cable breaks in insulated cables.

Application:

Three phase sequence testing, phase testing, testing of insulated cables and testing for open circuits.

Standard:

DIN EN 61010-1.

Supplied with:

2 batteries No. 081561 size LR3.

IP Index of Protection: IP 53

Voltage range AC: 200 - 1000 V

Overvoltage category: CAT IV / 600V

Power supply: 2x 081561 LR3

Technical description

Voltage range AC	200 - 1000 V
Height	25 mm
Power supply	2x 081561 LR3
Width	20 mm
Length	153 mm
Overvoltage category	CAT IV / 600V
IP Index of Protection	IP 53

Material of the housing	ABS plastic
Type of product	Phase and phase sequence tester

Accessories

Alkaline-manganese batteries International size LR3	081556 LR3
---	------------