

 Mahr**Digital dial indicator IP54 0.0005 mm reading, Measuring range: 25mm****Order data**

Order number	434316 25
GTIN	4059192014599
Item class	43A

Description**Version:**

Digital dial indicator with **very large** numeric display (**11 mm**) and integrated tolerance display (with or without measured value display). The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons.

Absolute function:

Zeroing in any position, without losing the reference value.

Factor adjustable with indication in display.

Individual functions can be blocked directly at the digital indicator. Settings and saved values (factor, preset, tolerances) are not lost even when changing the battery.

Dust-proof and splashproof version IP 54.**Function:**

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR 2450.

Optional extras:

Data cable No. 498940.

Technical description

Thickness of housing	35 mm
Gauging force	0.65-1.15 N
Clamping shank Ø h6	8 mm
Body Ø	58 mm
Calibration	C1
Measuring range	25 mm
Reversible reading	0.00002 in
Reversible reading	0.0005 mm
IP Index of Protection	IP 54
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2450
Power supply	Battery-powered
Measurement variation E MPE (measurement range)	0.004 mm
Standard	Manufacturer's standard
Reversible reading	mm / inch
Interface	Digimatic interface
Interface	USB interface
Interface	RS232 interface
Measured value saving	MAHR reference-lock system
Measurement technology	digital
Type of product	dial gauge

Services

Calibration Dial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 30 mm	023000 30
DAkkS calibration Dial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 100 mm	023010 100

Accessories

Button cell / special battery Battery type CR2450	081560 CR2450
Transmitter Type S4E	498966 S4E
Multi-receiver / USB keyboard interface Type	498975
Connection cablesimplex with data key Type R2	498940 R2
Connection cablesimplex with data key Type USB2	498940 USB2
Connection cablesimplex with data key Type D2	498940 D2
Receiver / USB keyboard interface Type	498965