

BENNING**Multimeter, Manufacturer's designation: MM1-3****Order data**

Order number	473300 MM1-3
GTIN	4014650440839
Item class	47A

Description**Version:**

Sturdy plastic casing with large-format, 3½ inch, 4 inch or 4¾ inch LCD display.

Application:

Digital service multimeters for a wide range of applications. These provide a high level of safety and other additional functions.

Standard:

IEC / DIN EN 061010-1 (DIN VDE 0411-1).

Supplied with:

Batteries, probe leads, compact protective case, operating instructions. Wire temperature sensor.

Rubber suspension device

Calibration: I3

Calibration: I7

Information displayed: 2000

Basic accuracy: 0.5 %

Continuity testing: yes

Diode testing: yes

Voltage sensor (non-contact): yes

Measurement process: RMS

Technical description

AC current	1 mA – 10 A
Capacitance	1 pF – 2 mF
Measurement process	RMS
AC voltage	0.1 mV – 750 V
Resistance	0.1 Ω – 20 M Ω
Frequency	1 Hz – 20 MHz
Memory function	HOLD, MAX / MIN
Voltage sensor (non-contact)	yes
Diode testing	yes
Temperature	-20 - 800 °C
Basic accuracy	0.5 %
Overvoltage category	CAT III 600 V
Continuity testing	yes
Manufacturer's designation	MM1-3
DC current	1 mA – 10 A
DC voltage	0.1 mV – 1000 V
Information displayed	2000
Calibration	I3
Calibration	I7
Number of batteries contained	2
Article no of the battery / rechargeable battery fitted	081561 LR3
Power supply	Battery-powered
Material of the housing	Plastic
Type of product	Multimeter

Services

Labelling laser-etched Type	018940
Calibration Digital multimeter Number of decimal places 3	017710 3
	016700 A

Calibration Temperature sensor with / without display Type A	
DAkKS calibration Temperature sensor with / without display Type A	016870 A
DAkKS calibration Digital multimeter Number of decimal places 3	016780 3
DAkKS recalibration Digital multimeter Number of decimal places 3	027010 3
Calibration Temperature sensor with / without display Type A	027520 A
DAkKS calibration Temperature sensor with / without display Type A	027540 A
Calibration Digital multimeter Number of decimal places 3	027000 3

Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
Alkaline-manganese batteries International size LR3	081556 LR3