

**BENNING****Multimeter, Manufacturer's designation: MM3****Order data**

Order number	473300 MM3
GTIN	4014651000537
Item class	47A

**Description****Version:**

Sturdy plastic casing with large-format, 3½ inch, 4 inch or 4¾ inch LCD display.

**Application:**

Digital service multimeters for a wide range of applications. These provide a high level of safety and other additional functions.

**Standard:**

**IEC / DIN EN 061010-1 (DIN VDE 0411-1).**

**Supplied with:**

Batteries, probe leads, compact protective case, operating instructions. Rubber protective surround.

Calibration: I3

Information displayed: 2000

Basic accuracy: 0.5 %

Continuity testing: yes

Diode testing: yes

Measurement process: RMS

AC voltage: 0.1 mV – 600 V

**Technical description**

Basic accuracy	0.5 %
Capacitance	1 pF – 200 µF
DC voltage	0.1 mV – 600 V
DC current	0.1 µA – 20 A
Diode testing	yes
Frequency	1 Hz – 200 kHz
AC current	0.1 µA – 20 A
Overvoltage category	CAT III 300 V CAT II 600 V
Manufacturer's designation	MM3
AC voltage	0.1 mV – 600 V
Information displayed	2000
Measurement process	RMS
Resistance	0.1 Ω – 20 MΩ
Continuity testing	yes
Calibration	I3
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081561 6LR61
Power supply	Battery-powered
Material of the housing	Plastic
Type of product	Multimeter

## Services

Calibration Digital multimeter Number of decimal places 3	017710 3
Labelling laser-etched Type	018940
DAkkS calibration Digital multimeter Number of decimal places 3	016780 3
DAkkS recalibration Digital multimeter Number of decimal places 3	027010 3
Calibration Digital multimeter Number of decimal places 3	027000 3

## Accessories

Alkaline-manganese batteries International size 6LR61

081556 6LR61