

BENNING

Multimeter, Manufacturer's designation: MM7-1



Order data

Order number	473300 MM7-1
GTIN	4014651440852
Item class	47A

Description

Version:

Sturdy plastic casing with large-format, 3½ inch, 4 inch or 4¾ inch LCD display.

Application:

Digital service multimeters for a wide range of applications. These provide a high level of safety and other additional functions. AutoV function for automatic AC/DC voltage detection and low input impedance (LoZ).

Standard:

IEC / DIN EN 061010-1 (DIN VDE 0411-1).

Supplied with:

Batteries, probe leads, compact protective case, operating instructions. Rubber protective surround.

Wire temperature sensor.

Technical description

AC current	10 µA – 10 A
DC current	10 µA – 10 A
Basic accuracy	0.08 %

Temperature	-40 - 400 °C
Diode testing	yes
Manufacturer's designation	MM7-1
Overvoltage category	CAT III 1000 V
Overvoltage category	CAT IV 600 V
Memory function	HOLD, MAX / MIN
DC voltage	0.01 mV – 1000 V
Voltage sensor (non-contact)	yes
Measurement process	TRUE RMS (AC+DC)
Information displayed	6000
AC voltage	0.01 mV – 1000 V
Resistance	0.1 Ω – 40 M Ω
Frequency	0.01 Hz – 100 kHz
Capacitance	1 nF – 10 mF
Continuity testing	yes
Calibration	I7
Calibration	I3
#Number of batteries contained	1
#Article no of the battery / rechargeable battery fitted	081561 6LR61
Power supply	Battery-powered
Material of the housing	Plastic
Type of product	Multimeter

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/473300-MM7-1>